



PEPLYN HA Filter Cartridges

- liquid filters
- polypropylene

Two ways to increase the lifetime of a filter are to increase the amount of contamination it can handle or to improve the effectiveness of cleaning procedures. PEPLYN HA combines both of these features in its advanced pleated construction.

PEPLYN HA utilizes polypropylene filter media and support materials, which balance a high surface area and closely controlled porosity, in a configuration that maximizes the cleaning efficiency of the cartridge.

Capture of larger particles is predominantly on the surface of the media, where the rigid, open pleat structure ensures that backwash cleaning provides effective removal. Smaller particles are retained throughout the depth of the graded density PEPLYN media, providing accurately defined retention under wide extremes of operating conditions.


Features and Benefits

- Ideally suited for raw water filtration where the longevity of the filter can be enhanced by repetitive backwashing
- Trap filtration (also known as police or guard filtration) removing precoat and body fed particles that have been released from powder filters, for example, in a brewing process
- Removal of carbon and resin fines downstream from treatment processes
- Clarification of CIP solutions prior to their use with fine prefilter cartridges and microporous membranes



Note: PEPLYN is a registered trademark of Parker domnick hunter

Performance Characteristics



For K size for a given flow rate multiply 10" size differential pressure by 2

10" Size (250 mm) Cartridge

Specifications

Materials of Construction

- Filtration Media: Polypropylene
- Upstream Support: Polypropylene
- Downstream Support: Polypropylene
- Inner Support Core: Polypropylene
- Outer Protection Cage: Polypropylene
- End Caps: Polypropylene
- End Cap Insert (if applicable): 316L Stainless Steel*
*Not available in B & L endcap variants
- Standard o-rings/gaskets: Silicone / EPDM
- Capsule Body: Polypropylene
- Capsule Vent Seals: Silicone

Food and Biological Safety

Materials conform to the relevant requirements of 21CFR Part 177, EC1935 / 2004 and current USP Plastics Class VI - 121 °C and ISO10993 equivalents.

Recommended Operating Conditions

Up to 70 °C (158 °F) continuous operating temperature and higher short-term temperatures during CIP to the following limits:

Temperature		Max. Forward dP	
°C	°F	(bar)	(psi)
20	68	5.0	72.5
40	104	4.0	58.0
60	140	3.0	43.5
80	176	2.0	29.0
90	194	1.0	14.5
>100 (steam)	>212 (steam)	0.3	4.0

Capsules may be operated up to a temperature of 40 °C (104 °F) at line pressures up to 5.0 barg (72.51 psig) for liquids.

Effective Filtration Area (EFA)

10" (250 mm) Up to 0.7 m² (7.53 ft²)

Cleaning and Sterilization

PEPLYN HA cartridges can be repeatedly steam sterilized in situ or autoclaved at up to 135 °C (275 °F). They can be sanitized with hot water at up to 90 °C (194 °F) and are compatible with a wide range of chemicals. Capsules can be repeatedly autoclaved up to 135 °C (275 °F).

Retention Characteristics

The retention characteristics of PEPLYN HA filter cartridges have been determined by a single-pass technique using suspensions of ISO 12103 Pt. 1 A2 Fine and A4 Course test dust in water.

Efficiency Beta Ratio	Micron Rating at Various Efficiencies					
	>99.99%	99.98%	99.90%	99%	95%	90%
D	1.00	0.95	0.90	0.70	0.60	0.50
E	1.50	1.40	1.10	0.80	0.70	0.60
G	3.00	2.80	1.80	1.00	0.90	0.70
H	5.00	4.70	4.50	3.50	2.30	1.00
K	10.00	8.00	7.00	4.80	3.80	2.80
L	15.00	12.00	10.00	7.20	6.00	4.50
M	20.00	16.00	14.00	10.00	8.00	6.00
N	25.00	20.00	17.00	12.00	9.00	7.00
P	32.00	27.00	24.00	18.00	13.00	10.00
T	50.00	40.00	34.00	28.00	20.00	17.00
U	70.00	55.00	50.00	40.00	30.00	25.00
W	125.00	100.00	80.00	70.00	50.00	40.00

Ordering Information

Cartridges

Code Length (Nominal)		Retention Rating	Code Flush	Code Endcap (10")	Code Format	Code O-rings
B*	2.5" (65 mm)	D	N None	B* dh DOE	A 10" Modular	E EPDM
A*	5" (125 mm)	E	For detailed operational procedures and advice on cleaning and sterilization, please contact the Technical Support Group through your usual Parker domnick hunter contact.	C BF / 226 Bayonet	D Demi	S Silicone
K	5" (125 mm)	G		D Fin / 222		
1	10" (250 mm)	H		E Flat Top / 222		
2	20" (500 mm)	K		G Recess / 222		
3	30" (750 mm)	L		H UF Retrofit		
4	40" (1000 mm)	M		J SOE (no o-ring)		
		N		L* dh DOE		
		P		N Internal 213		
		T		R BF / 222 Bayonet		
		U				
		W*				
				Code Endcap (Demi)		
				SK Retrofit		
				T TRUESEAL		
				Y Demi Stub		
				Z Demi A & B Std		

* Supplied in packs of 3.

* Not available in A and B lengths.

* EPDM gaskets supplied as standard

Capsules

Code Length (Nominal)		Retention Rating	Code Flush	Code Inlet Connection	Code Outlet Connection	Code Vent / Drain Seals
E	4.4" (113 mm)	D	N None	T 1" Tri-Clamp	T 1" Tri-Clamp	S Silicone
B	5.5" (140 mm)	E		N 1/2" NPT Male	N 1/2" NPT Male	
A	7.9" (200 mm)	H		H 1/2" Hosebarb	H 1/2" Hosebarb	
		K		G Stepped Hosebarb	G Stepped Hosebarb	
		L		M 1/4" NPT Male	M 1/4" NPT Male	
		M		V 3/8" NPT Female	V 3/8" NPT Female	
		N				
		P				
		T				
		U				

Supplied in packs of 3.